

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279150

Luminaire Tested: **LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279150  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1719.1 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279150

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279150

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4400195
5°	4058098
10°	2734610
15°	1348268
20°	575900
25°	226401
30°	89156
35°	39088
40°	18806
45°	9070
50°	4989
55°	2752
60°	1579
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P279150

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	694.1	40.4
10°-20°	747.5	43.5
20°-30°	215.8	12.6
30°-40°	45.6	2.7
40°-50°	11.2	0.7
50°-60°	3.2	0.2
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1657.5	96.4
0°-40°	1703.0	99.1
0°-60°	1717.5	99.9
0°-90°	1719.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1719.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8919	
5°	8194	694
15°	2640	748
25°	416	216
35°	65	46
45°	13	11
55°	3	3
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279150

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8918.8
1°	8862.9
2°	8768.1
3°	8640.0
4°	8458.4
5°	8194.1
6°	7837.3
7°	7372.0
8°	6799.6
9°	6132.4
10°	5458.6
11°	4777.6
12°	4134.7
13°	3564.0
14°	3062.1
15°	2639.7
17.5°	1744.7
20°	1096.9
22.5°	674.5
25°	415.9
27.5°	253.8
30°	156.5
32.5°	98.9
35°	64.9
37.5°	43.0
40°	29.2
42.5°	20.3
45°	13.0
47.5°	8.1
50°	6.5
52.5°	4.9
55°	3.2
57.5°	2.4
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.8
80°	0.0
82.5°	0.0



TEST NUMBER: P279150

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)