

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280932

Luminaire Tested: **LDA2B209050D010 EU2B20WFL559050 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1887.8 lumens  
Efficiency: N/A  
Efficacy: 91.6 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280932

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P280932

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1612208
5°	1579341
10°	1468652
15°	1282328
20°	1061652
25°	811974
30°	444354
35°	164484
40°	56933
45°	25676
50°	12127
55°	6021
60°	1776
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280932

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	296.3	15.7
10°-20°	693.9	36.8
20°-30°	655.9	34.7
30°-40°	201.9	10.7
40°-50°	31.9	1.7
50°-60°	6.8	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1646.1	87.2
0°-40°	1848.0	97.9
0°-60°	1886.6	99.9
0°-90°	1887.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1887.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3268	
5°	3189	296
15°	2511	694
25°	1492	656
35°	273	202
45°	37	32
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280932

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3267.8
1°	3255.5
2°	3240.6
3°	3228.4
4°	3212.6
5°	3189.0
6°	3158.4
7°	3117.2
8°	3062.1
9°	2998.2
10°	2931.6
11°	2858.1
12°	2780.2
13°	2695.3
14°	2606.9
15°	2510.6
17.5°	2255.8
20°	2022.1
22.5°	1784.9
25°	1491.6
27.5°	1138.0
30°	780.0
32.5°	478.8
35°	273.1
37.5°	152.3
40°	88.4
42.5°	55.1
45°	36.8
47.5°	24.5
50°	15.8
52.5°	10.5
55°	7.0
57.5°	4.4
60°	1.8
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280932

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)