

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280941

Luminaire Tested: **LDA2B209050D010 EU2B20WFL559050 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20WFL559050 2LBALD1B
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1841.8 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280941

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P280941

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1572936
5°	1540909
10°	1432932
15°	1251121
20°	1035821
25°	792214
30°	433530
35°	160509
40°	55580
45°	25048
50°	11820
55°	5849
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280941

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.1	15.7
10°-20°	677.0	36.8
20°-30°	639.9	34.7
30°-40°	197.0	10.7
40°-50°	31.1	1.7
50°-60°	6.6	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1606.0	87.2
0°-40°	1803.0	97.9
0°-60°	1840.7	99.9
0°-90°	1841.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1841.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3188	
5°	3111	289
15°	2450	677
25°	1455	640
35°	266	197
45°	36	31
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280941

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3188.2
1°	3176.3
2°	3161.8
3°	3149.8
4°	3134.4
5°	3111.4
6°	3081.5
7°	3041.3
8°	2987.5
9°	2925.2
10°	2860.3
11°	2788.5
12°	2712.5
13°	2629.7
14°	2543.4
15°	2449.5
17.5°	2200.9
20°	1972.9
22.5°	1741.4
25°	1455.3
27.5°	1110.3
30°	761.0
32.5°	467.2
35°	266.5
37.5°	148.6
40°	86.3
42.5°	53.8
45°	35.9
47.5°	23.9
50°	15.4
52.5°	10.2
55°	6.8
57.5°	4.3
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280941

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)