

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280939

Luminaire Tested: **LDA2B209050D010 EU2B20WFL559050 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20WFL559050 2LBALD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1849.4 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280939

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280939

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1579399
5°	1547199
10°	1438794
15°	1256228
20°	1040074
25°	795480
30°	435296
35°	161171
40°	55774
45°	25118
50°	11820
55°	5935
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280939

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.3	15.7
10°-20°	679.8	36.8
20°-30°	642.5	34.7
30°-40°	197.8	10.7
40°-50°	31.2	1.7
50°-60°	6.6	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1612.6	87.2
0°-40°	1810.4	97.9
0°-60°	1848.3	99.9
0°-90°	1849.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1849.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3201	
5°	3124	290
15°	2460	680
25°	1461	643
35°	268	198
45°	36	31
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280939

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3201.3
1°	3189.3
2°	3174.7
3°	3162.7
4°	3147.3
5°	3124.1
6°	3094.1
7°	3053.8
8°	2999.8
9°	2937.2
10°	2872.0
11°	2800.0
12°	2723.7
13°	2640.5
14°	2553.9
15°	2459.5
17.5°	2210.0
20°	1981.0
22.5°	1748.6
25°	1461.3
27.5°	1114.8
30°	764.1
32.5°	469.1
35°	267.6
37.5°	149.2
40°	86.6
42.5°	54.0
45°	36.0
47.5°	24.0
50°	15.4
52.5°	10.3
55°	6.9
57.5°	4.3
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280939

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)