

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278178

Luminaire Tested: **LDA2B159730D010 EU2B15SP159730 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159730D010 EU2B15SP159730 2LBAD1H
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1065.8 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278178

CATALOG NUMBER: LDA2B159730D010 EU2B15SP159730 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P278178

CATALOG NUMBER: LDA2B159730D010 EU2B15SP159730 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93	93	93	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92	92	92	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90	90	90	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88	88	88	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86	86	86	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	85	85	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82	82	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4815014
5°	3838803
10°	1666586
15°	575786
20°	236104
25°	106641
30°	42897
35°	19996
40°	10820
45°	4047
50°	2456
55°	1806
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278178

CATALOG NUMBER: LDA2B159730D010 EU2B15SP159730 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	585.8	55.0
10°-20°	351.8	33.0
20°-30°	96.8	9.1
30°-40°	23.0	2.2
40°-50°	5.7	0.5
50°-60°	1.9	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.5	97.1
0°-40°	1057.5	99.2
0°-60°	1065.1	99.9
0°-90°	1065.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1065.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9760	
5°	7751	586
15°	1127	352
25°	196	97
35°	33	23
45°	6	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278178

CATALOG NUMBER: LDA2B159730D010 EU2B15SP159730 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9759.6
1°	9651.7
2°	9393.1
3°	8998.7
4°	8442.2
5°	7751.3
6°	6907.8
7°	5983.7
8°	5012.8
9°	4119.7
10°	3326.7
11°	2655.4
12°	2113.6
13°	1704.4
14°	1379.0
15°	1127.3
17.5°	699.8
20°	449.7
22.5°	294.9
25°	195.9
27.5°	125.8
30°	75.3
32.5°	47.4
35°	33.2
37.5°	24.2
40°	16.8
42.5°	10.0
45°	5.8
47.5°	4.2
50°	3.2
52.5°	2.6
55°	2.1
57.5°	1.6
60°	1.1
62.5°	1.1
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278178

CATALOG NUMBER: LDA2B159730D010 EU2B15SP159730 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)