

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280740

Luminaire Tested: **LDA2B159730D010 EU2B15WFL559730 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1143.4 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280740

CATALOG NUMBER: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P280740

CATALOG NUMBER: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	976511
5°	956618
10°	889577
15°	776721
20°	643050
25°	491833
30°	269119
35°	99618
40°	34520
45°	15559
50°	7292
55°	3613
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280740

CATALOG NUMBER: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.5	15.7
10°-20°	420.3	36.8
20°-30°	397.3	34.7
30°-40°	122.3	10.7
40°-50°	19.3	1.7
50°-60°	4.1	0.4
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	997.0	87.2
0°-40°	1119.3	97.9
0°-60°	1142.8	99.9
0°-90°	1143.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1143.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1979	
5°	1932	179
15°	1521	420
25°	904	397
35°	165	122
45°	22	19
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280740

CATALOG NUMBER: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1979.3
1°	1971.9
2°	1962.9
3°	1955.5
4°	1945.9
5°	1931.6
6°	1913.1
7°	1888.1
8°	1854.7
9°	1816.0
10°	1775.7
11°	1731.2
12°	1684.0
13°	1632.6
14°	1579.0
15°	1520.7
17.5°	1366.4
20°	1224.8
22.5°	1081.1
25°	903.5
27.5°	689.3
30°	472.4
32.5°	290.0
35°	165.4
37.5°	92.3
40°	53.6
42.5°	33.4
45°	22.3
47.5°	14.8
50°	9.5
52.5°	6.4
55°	4.2
57.5°	2.7
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280740

CATALOG NUMBER: LDA2B159730D010 EU2B15WFL559730 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)