

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279977

Luminaire Tested: **LDA2B209027D010 EU2B20FL409027 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1642.1 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279977

CATALOG NUMBER: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P279977

CATALOG NUMBER: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96													96															
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92													92															
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89													89															
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85													85															
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82													82															
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79													79															
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77													77															
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74													74															
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72													72															
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69													69															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2257821
5°	2210037
10°	2014311
15°	1573567
20°	931656
25°	346325
30°	108240
35°	48122
40°	22348
45°	10536
50°	5757
55°	3269
60°	1480
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P279977

CATALOG NUMBER: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.5	25.1
10°-20°	820.3	50.0
20°-30°	336.0	20.5
30°-40°	55.6	3.4
40°-50°	13.2	0.8
50°-60°	3.5	0.2
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1568.8	95.5
0°-40°	1624.4	98.9
0°-60°	1641.1	99.9
0°-90°	1642.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4576	
5°	4462	413
15°	3081	820
25°	636	336
35°	80	56
45°	15	13
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279977

CATALOG NUMBER: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4576.4
1°	4560.5
2°	4539.4
3°	4520.6
4°	4495.7
5°	4462.5
6°	4413.5
7°	4349.5
8°	4258.3
9°	4147.4
10°	4020.8
11°	3873.8
12°	3708.0
13°	3518.8
14°	3308.5
15°	3080.8
17.5°	2443.1
20°	1774.5
22.5°	1136.0
25°	636.2
27.5°	335.4
30°	190.0
32.5°	120.6
35°	79.9
37.5°	52.8
40°	34.7
42.5°	22.6
45°	15.1
47.5°	10.6
50°	7.5
52.5°	5.3
55°	3.8
57.5°	2.3
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279977

CATALOG NUMBER: LDA2B209027D010 EU2B20FL409027 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)