

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499846

Luminaire Tested: **LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-15)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.8 lumens
Efficiency: N/A
Efficacy: 50.9 lumens/watt
Spacing Criteria (0/90/45): 3.2 / 0.53 / 1.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499846

CATALOG NUMBER: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P499846

CATALOG NUMBER: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90					90			
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80					80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71					71			
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63					63			
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56					56			
6	77	66	58	52	76	65	58	52	63	57	52	62	56	51	60	55	51	49					49			
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44					44			
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39					39			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	7943	7943	7943
5°	17284	7231	5151
10°	51901	6262	3407
15°	314734	4495	2656
20°	1126860	2468	1103
25°	1831297	871	0
30°	2009849	285	0
35°	1826425	0	0
40°	1567653	0	0
45°	1161981	0	0
50°	785725	0	0
55°	265442	430	0
60°	37989	987	0
65°	3035	1167	0
70°	0	1442	0
75°	0	3050	0
80°	0	2841	0
85°	0	5661	0



TEST NUMBER: P499846

CATALOG NUMBER: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.1	0.3
10°-20°	37.0	5.2
20°-30°	209.9	29.2
30°-40°	273.5	38.1
40°-50°	160.2	22.3
50°-60°	32.3	4.5
60°-70°	1.2	0.2
70°-80°	0.8	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.0	34.7
0°-40°	522.5	72.8
0°-60°	715.1	99.6
0°-90°	717.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	16	16	16	16	16	
5°	35	25	15	11	10	5
15°	616	70	9	6	5	261
25°	3364	118	2	1	0	1488
35°	3032	86	0	0	0	1888
45°	1665	21	0	0	0	1301
55°	309	2	0	0	0	360
65°	3	0	1	1	0	7
75°	0	1	2	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P499846

CATALOG NUMBER: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1
2.5°	21.9	20.3	19.3	16.7	15.1	14.1	13.5	13.0	12.5
5°	34.9	32.3	25.0	18.2	14.6	12.5	11.4	10.4	10.4
7.5°	59.8	48.4	32.8	19.3	13.5	10.9	9.9	8.3	7.8
10°	103.6	80.7	44.8	20.3	12.5	9.9	7.8	7.3	6.8
12.5°	243.0	147.3	56.7	20.3	10.9	8.3	6.8	6.2	5.7
15°	616.2	300.3	70.3	19.3	8.8	6.2	5.7	5.2	5.2
17.5°	1278.2	616.7	85.4	17.7	7.3	4.7	4.2	3.6	3.6
20°	2146.3	1105.4	99.9	15.1	4.7	3.1	2.6	2.1	2.1
21°	2465.8	1282.9	107.2	14.1	4.2	2.6	2.1	2.1	1.6
22°	2753.1	1445.8	111.4	13.5	3.1	2.1	2.1	1.6	1.6
23°	2938.4	1652.4	115.0	12.0	2.6	1.6	1.6	1.0	0.5
24°	3217.8	1814.2	116.6	10.9	2.1	1.6	1.0	0.5	0.5
25°	3364.1	1961.0	118.1	9.9	1.6	1.6	1.0	0.5	0.0
26°	3469.2	2077.0	123.9	9.4	1.6	1.0	1.0	0.5	0.0
27°	3551.4	2150.9	127.0	8.3	1.0	1.0	1.0	0.0	0.0
28°	3546.7	2204.5	124.4	7.3	1.0	1.0	0.5	0.0	0.0
29°	3569.1	2241.0	122.8	6.2	0.5	0.5	0.5	0.0	0.0
30°	3528.0	2244.1	117.1	5.7	0.5	0.5	0.5	0.0	0.0
31°	3465.5	2206.1	115.0	5.2	0.0	0.5	0.5	0.0	0.0
32°	3406.7	2188.9	108.2	4.2	0.0	0.5	0.5	0.0	0.0
33°	3305.8	2111.9	101.5	3.6	0.0	0.5	0.0	0.0	0.0
34°	3170.5	2036.4	95.2	3.1	0.0	0.5	0.0	0.0	0.0
35°	3032.5	1974.0	86.4	3.1	0.0	0.5	0.0	0.0	0.0
36°	2918.1	1860.5	80.1	2.6	0.0	0.5	0.0	0.0	0.0
37°	2779.1	1763.2	71.8	2.1	0.0	0.0	0.0	0.0	0.0
38°	2684.4	1626.3	65.6	2.1	0.0	0.0	0.0	0.0	0.0
39°	2556.9	1510.8	57.8	1.6	0.0	0.0	0.0	0.0	0.0
40°	2434.1	1391.1	50.0	1.0	0.0	0.0	0.0	0.0	0.0
42.5°	2081.7	1073.1	34.3	0.5	0.0	0.0	0.0	0.0	0.0
45°	1665.4	786.9	21.3	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	1322.4	531.4	13.5	0.0	0.0	0.0	0.0	0.0	0.0
50°	1023.7	273.7	7.8	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	680.7	116.1	4.7	0.0	0.0	0.5	0.0	0.0	0.0
55°	308.6	60.4	2.1	0.0	0.5	0.5	0.5	0.0	0.0
57.5°	124.4	26.0	1.0	0.5	0.5	0.5	0.5	0.0	0.0
60°	38.5	7.3	0.5	0.5	1.0	1.0	0.5	0.0	0.0
62.5°	7.8	1.6	0.5	1.0	1.0	1.0	0.5	0.0	0.0
65°	2.6	0.5	0.5	1.0	1.0	1.0	1.0	0.0	0.0
67.5°	0.5	0.5	0.5	1.0	1.0	1.0	1.0	0.5	0.0
70°	0.0	0.5	1.0	1.0	1.0	1.6	1.0	0.5	0.0
72.5°	0.0	0.5	1.0	1.0	1.0	1.0	1.0	0.5	0.0
75°	0.0	0.5	1.0	1.0	1.6	1.6	1.0	0.5	0.0
77.5°	0.0	0.5	1.0	1.0	1.0	1.0	1.0	0.5	0.0
80°	0.0	0.5	1.0	1.0	1.0	1.0	1.0	0.5	0.0



TEST NUMBER: P499846

CATALOG NUMBER: LDA2B159730R30D010 2LBDLC1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.5	1.0	1.0	1.0	1.0	1.0	0.5	0.0
85°	0.0	0.5	1.0	1.0	1.0	1.0	1.0	0.0	0.0
87.5°	0.0	0.5	1.0	1.0	1.0	1.0	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)