

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499940

Luminaire Tested: **LDA2B159730R65D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159730R65D010 2LBD1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1053.7 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499940  
CATALOG NUMBER: LDA2B159730R65D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P499940

CATALOG NUMBER: LDA2B159730R65D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	572596
5°	526546
10°	503177
15°	483235
20°	445116
25°	412193
30°	377701
35°	277412
40°	131384
45°	43189
50°	13969
55°	1806
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P499940

CATALOG NUMBER: LDA2B159730R65D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.9	9.5
10°-20°	263.1	25.0
20°-30°	349.0	33.1
30°-40°	276.1	26.2
40°-50°	60.3	5.7
50°-60°	4.5	0.4
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	712.1	67.6
0°-40°	988.2	93.8
0°-60°	1053.0	99.9
0°-90°	1053.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1053.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1161	
5°	1063	100
15°	946	263
25°	757	349
35°	461	276
45°	62	60
55°	2	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499940

CATALOG NUMBER: LDA2B159730R65D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1160.6
1°	1154.3
2°	1133.0
3°	1109.6
4°	1085.1
5°	1063.2
6°	1049.2
7°	1035.1
8°	1025.8
9°	1011.7
10°	1004.4
11°	993.0
12°	980.0
13°	968.5
14°	955.5
15°	946.1
16°	922.2
17°	910.2
18°	890.5
19°	872.2
20°	847.8
21°	828.0
22.5°	802.0
23°	794.7
24°	774.9
25°	757.2
26°	746.3
27°	728.1
28°	710.4
29°	689.0
30°	663.0
32.5°	572.5
35°	460.6
37.5°	328.4
40°	204.0
42.5°	115.0
45°	61.9
47.5°	33.3
50°	18.2
52.5°	7.8
55°	2.1
57.5°	1.0
60°	1.0
62.5°	0.5
65°	0.5



TEST NUMBER: P499940

CATALOG NUMBER: LDA2B159730R65D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)