

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280879

Luminaire Tested: **LDA2B209027D010 EU2B20WFL559027 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280879  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1639.0 lumens  
Efficiency: N/A  
Efficacy: 79.6 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280879

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P280879

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76		
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72		
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62		
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1399766
5°	1371238
10°	1275176
15°	1113367
20°	921786
25°	705006
30°	385791
35°	142801
40°	49462
45°	22257
50°	10515
55°	5247
60°	1480
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P280879

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.3	15.7
10°-20°	602.5	36.8
20°-30°	569.4	34.7
30°-40°	175.3	10.7
40°-50°	27.7	1.7
50°-60°	5.9	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.2	87.2
0°-40°	1604.5	97.9
0°-60°	1638.0	99.9
0°-90°	1639.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1639.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2837	
5°	2769	257
15°	2180	602
25°	1295	569
35°	237	175
45°	32	28
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280879

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2837.2
1°	2826.6
2°	2813.6
3°	2803.0
4°	2789.3
5°	2768.8
6°	2742.2
7°	2706.5
8°	2658.6
9°	2603.1
10°	2545.4
11°	2481.5
12°	2413.9
13°	2340.1
14°	2263.4
15°	2179.8
17.5°	1958.6
20°	1755.7
22.5°	1549.7
25°	1295.1
27.5°	988.0
30°	677.2
32.5°	415.7
35°	237.1
37.5°	132.2
40°	76.8
42.5°	47.9
45°	31.9
47.5°	21.3
50°	13.7
52.5°	9.1
55°	6.1
57.5°	3.8
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280879

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)