

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499983

Luminaire Tested: **LDA2B159730R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499983  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159730R70D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1020.6 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499983

CATALOG NUMBER: LDA2B159730R70D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P499983

CATALOG NUMBER: LDA2B159730R70D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		81	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	404063
5°	401694
10°	399025
15°	391604
20°	377440
25°	361349
30°	344204
35°	284037
40°	184646
45°	96495
50°	44901
55°	16429
60°	1677
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499983

CATALOG NUMBER: LDA2B159730R70D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.7	7.5
10°-20°	215.5	21.1
20°-30°	305.8	30.0
30°-40°	286.0	28.0
40°-50°	115.0	11.3
50°-60°	20.1	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.0	58.6
0°-40°	883.9	86.6
0°-60°	1019.1	99.9
0°-90°	1020.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	819	
5°	811	77
15°	767	215
25°	664	306
35°	472	286
45°	138	115
55°	19	20
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P499983

CATALOG NUMBER: LDA2B159730R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	819.0
1°	820.1
2°	818.4
3°	815.0
4°	813.3
5°	811.1
6°	802.1
7°	804.9
8°	797.0
9°	795.3
10°	796.5
11°	789.2
12°	787.5
13°	778.5
14°	775.1
15°	766.7
16°	761.6
17°	751.5
18°	739.7
19°	733.0
20°	718.9
21°	708.2
22.5°	688.6
23°	683.5
24°	673.9
25°	663.8
26°	656.0
27°	644.7
28°	633.5
29°	620.0
30°	604.2
32.5°	549.2
35°	471.6
37.5°	380.0
40°	286.7
42.5°	204.6
45°	138.3
47.5°	91.1
50°	58.5
52.5°	36.5
55°	19.1
57.5°	6.2
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P499983

CATALOG NUMBER: LDA2B159730R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)