

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280878

Luminaire Tested: **LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1639.0 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280878

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P280878

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 98 | 95 | 97 | 95 | 93 | 95 | 93 | 91 | 90 | | | |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 91 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | | | |
| 4 | 100 | 94 | 89 | 85 | 99 | 93 | 88 | 85 | 91 | 87 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 80 | | | |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 83 | 80 | 86 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 78 | 76 | | | |
| 6 | 92 | 84 | 79 | 75 | 91 | 84 | 79 | 75 | 82 | 78 | 75 | 81 | 77 | 74 | 80 | 76 | 74 | 72 | | | |
| 7 | 88 | 80 | 75 | 71 | 87 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | | | |
| 8 | 85 | 76 | 71 | 68 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | | |
| 9 | 81 | 73 | 68 | 64 | 80 | 72 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 64 | 62 | | | |
| 10 | 78 | 70 | 65 | 61 | 77 | 69 | 64 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 61 | 59 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1399766 |
| 5° | 1371238 |
| 10° | 1275176 |
| 15° | 1113367 |
| 20° | 921786 |
| 25° | 705006 |
| 30° | 385791 |
| 35° | 142801 |
| 40° | 49462 |
| 45° | 22257 |
| 50° | 10515 |
| 55° | 5247 |
| 60° | 1480 |
| 65° | 934 |
| 70° | 1154 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P280878

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 257.3 | 15.7 |
| 10°-20° | 602.5 | 36.8 |
| 20°-30° | 569.4 | 34.7 |
| 30°-40° | 175.3 | 10.7 |
| 40°-50° | 27.7 | 1.7 |
| 50°-60° | 5.9 | 0.4 |
| 60°-70° | 0.9 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1429.2 | 87.2 |
| 0°-40° | 1604.5 | 97.9 |
| 0°-60° | 1638.0 | 99.9 |
| 0°-90° | 1639.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1639.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2837 | |
| 5° | 2769 | 257 |
| 15° | 2180 | 602 |
| 25° | 1295 | 569 |
| 35° | 237 | 175 |
| 45° | 32 | 28 |
| 55° | 6 | 6 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P280878

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2837.2 |
| 1° | 2826.6 |
| 2° | 2813.6 |
| 3° | 2803.0 |
| 4° | 2789.3 |
| 5° | 2768.8 |
| 6° | 2742.2 |
| 7° | 2706.5 |
| 8° | 2658.6 |
| 9° | 2603.1 |
| 10° | 2545.4 |
| 11° | 2481.5 |
| 12° | 2413.9 |
| 13° | 2340.1 |
| 14° | 2263.4 |
| 15° | 2179.8 |
| 17.5° | 1958.6 |
| 20° | 1755.7 |
| 22.5° | 1549.7 |
| 25° | 1295.1 |
| 27.5° | 988.0 |
| 30° | 677.2 |
| 32.5° | 415.7 |
| 35° | 237.1 |
| 37.5° | 132.2 |
| 40° | 76.8 |
| 42.5° | 47.9 |
| 45° | 31.9 |
| 47.5° | 21.3 |
| 50° | 13.7 |
| 52.5° | 9.1 |
| 55° | 6.1 |
| 57.5° | 3.8 |
| 60° | 1.5 |
| 62.5° | 0.8 |
| 65° | 0.8 |
| 67.5° | 0.8 |
| 70° | 0.8 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P280878

CATALOG NUMBER: LDA2B209027D010 EU2B20WFL559027 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)