

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278970

Luminaire Tested: **LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1052.2 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278970

CATALOG NUMBER: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P278970

CATALOG NUMBER: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2693213
5°	2483809
10°	1673800
15°	825244
20°	352502
25°	138595
30°	54576
35°	23911
40°	11528
45°	5512
50°	3070
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278970

CATALOG NUMBER: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	424.8	40.4
10°-20°	457.5	43.5
20°-30°	132.1	12.6
30°-40°	27.9	2.7
40°-50°	6.9	0.7
50°-60°	2.0	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1014.5	96.4
0°-40°	1042.4	99.1
0°-60°	1051.2	99.9
0°-90°	1052.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1052.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5459	
5°	5015	425
15°	1616	458
25°	255	132
35°	40	28
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278970

CATALOG NUMBER: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5458.9
1°	5424.7
2°	5366.6
3°	5288.2
4°	5177.1
5°	5015.3
6°	4797.0
7°	4512.1
8°	4161.8
9°	3753.4
10°	3341.1
11°	2924.2
12°	2530.7
13°	2181.4
14°	1874.2
15°	1615.7
17.5°	1067.9
20°	671.4
22.5°	412.9
25°	254.6
27.5°	155.3
30°	95.8
32.5°	60.5
35°	39.7
37.5°	26.3
40°	17.9
42.5°	12.4
45°	7.9
47.5°	5.0
50°	4.0
52.5°	3.0
55°	2.0
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278970

CATALOG NUMBER: LDA2B15D2WD010 EU2B15NFL25D2W 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)