

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280052

Luminaire Tested: **LDA2B209727D010 EU2B20FL409727 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209727D010 EU2B20FL409727 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1497.8 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280052

CATALOG NUMBER: LDA2B209727D010 EU2B20FL409727 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P280052

CATALOG NUMBER: LDA2B209727D010 EU2B20FL409727 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96	96	96	96	96	96	96	96	96																
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92	92	92	92	92	92	92	92	92																
	3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85	85	85	85	85	85	85	85	85	85	85	85																
	5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82	82	82	82	82	82	82	82	82	82	82	82																
	6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79	79	79	79	79	79	79	79	79	79	79	79																
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77	77	77	77	77	77	77	77	77	77	77	77																
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74	74	74	74	74	74	74																
	9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72	72	72	72	72	72	72	72	72	72	72	72																
	10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69	69	69	69	69	69	69	69	69	69	69	69																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2059440
5°	2015900
10°	1837367
15°	1435354
20°	849805
25°	315895
30°	98726
35°	43906
40°	20352
45°	9629
50°	5296
55°	2925
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280052

CATALOG NUMBER: LDA2B209727D010 EU2B20FL409727 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.3	25.1
10°-20°	748.3	50.0
20°-30°	306.5	20.5
30°-40°	50.7	3.4
40°-50°	12.0	0.8
50°-60°	3.2	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1431.0	95.5
0°-40°	1481.7	98.9
0°-60°	1496.9	99.9
0°-90°	1497.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1497.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4174	
5°	4070	376
15°	2810	748
25°	580	306
35°	73	51
45°	14	12
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280052

CATALOG NUMBER: LDA2B209727D010 EU2B20FL409727 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4174.3
1°	4159.9
2°	4140.6
3°	4123.4
4°	4100.8
5°	4070.5
6°	4025.8
7°	3967.4
8°	3884.2
9°	3783.1
10°	3667.6
11°	3533.5
12°	3382.2
13°	3209.6
14°	3017.8
15°	2810.2
17.5°	2228.5
20°	1618.6
22.5°	1036.2
25°	580.3
27.5°	306.0
30°	173.3
32.5°	110.0
35°	72.9
37.5°	48.1
40°	31.6
42.5°	20.6
45°	13.8
47.5°	9.6
50°	6.9
52.5°	4.8
55°	3.4
57.5°	2.1
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280052

CATALOG NUMBER: LDA2B209727D010 EU2B20FL409727 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)