

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280958

Luminaire Tested: **LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280958  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1474.7 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280958

CATALOG NUMBER: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P280958

CATALOG NUMBER: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1259454
5°	1233807
10°	1147328
15°	1001765
20°	829381
25°	634348
30°	347109
35°	128527
40°	44503
45°	20025
50°	9441
55°	4731
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280958

CATALOG NUMBER: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.5	15.7
10°-20°	542.1	36.8
20°-30°	512.4	34.7
30°-40°	157.7	10.7
40°-50°	24.9	1.7
50°-60°	5.3	0.4
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.9	87.2
0°-40°	1443.7	97.9
0°-60°	1473.9	99.9
0°-90°	1474.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1474.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2553	
5°	2491	231
15°	1961	542
25°	1165	512
35°	213	158
45°	29	25
55°	6	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280958

CATALOG NUMBER: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2552.8
1°	2543.3
2°	2531.6
3°	2522.1
4°	2509.8
5°	2491.3
6°	2467.4
7°	2435.2
8°	2392.1
9°	2342.2
10°	2290.2
11°	2232.8
12°	2171.9
13°	2105.6
14°	2036.5
15°	1961.3
17.5°	1762.3
20°	1579.7
22.5°	1394.4
25°	1165.3
27.5°	889.0
30°	609.3
32.5°	374.1
35°	213.4
37.5°	119.0
40°	69.1
42.5°	43.1
45°	28.7
47.5°	19.1
50°	12.3
52.5°	8.2
55°	5.5
57.5°	3.4
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280958

CATALOG NUMBER: LDA2B209727D010 EU2B20WFL559727 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)