

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500110

Luminaire Tested: **LDA2B208027R45D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208027R45D010 2LBD1GPH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1983.1 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500110  
CATALOG NUMBER: LDA2B208027R45D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P500110

CATALOG NUMBER: LDA2B208027R45D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85		90	87	84		88	86	84	82
5	97	90	86	82	96	90	85	82	88	84	81		86	83	80		85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77		83	79	76		82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		78	75	73	71
8	87	79	74	70	86	78	74	70	77	73	70		76	73	70		76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67		73	70	67		73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64		71	67	64		70	67	64	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1968168
5°	1938147
10°	1808662
15°	1578419
20°	1206927
25°	700924
30°	297319
35°	123107
40°	54357
45°	28118
50°	13969
55°	3269
60°	1875
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500110

CATALOG NUMBER: LDA2B208027R45D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	364.2	18.4
10°-20°	842.8	42.5
20°-30°	589.3	29.7
30°-40°	145.9	7.4
40°-50°	33.8	1.7
50°-60°	5.5	0.3
60°-70°	1.1	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1796.3	90.6
0°-40°	1942.2	97.9
0°-60°	1981.6	99.9
0°-90°	1983.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1983.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3989	
5°	3914	364
15°	3090	843
25°	1288	589
35°	204	146
45°	40	34
55°	4	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500110

CATALOG NUMBER: LDA2B208027R45D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3989.3
1°	3980.7
2°	3978.8
3°	3966.3
4°	3930.8
5°	3913.5
6°	3878.0
7°	3827.2
8°	3764.8
9°	3700.5
10°	3610.3
11°	3536.5
12°	3446.3
13°	3329.2
14°	3210.3
15°	3090.3
16°	2957.9
17°	2800.6
18°	2641.3
19°	2477.3
20°	2298.8
21°	2084.8
22.5°	1807.6
23°	1693.4
24°	1488.1
25°	1287.6
26°	1099.5
27°	923.9
28°	769.5
29°	635.1
30°	521.9
32.5°	321.4
35°	204.4
37.5°	132.4
40°	84.4
42.5°	57.6
45°	40.3
47.5°	28.8
50°	18.2
52.5°	9.6
55°	3.8
57.5°	1.9
60°	1.9
62.5°	1.0
65°	1.0



TEST NUMBER: P500110

CATALOG NUMBER: LDA2B208027R45D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)