

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500128

Luminaire Tested: **LDA2B208027R45D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208027R45D010 2LBDL1WMH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1853.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500128

CATALOG NUMBER: LDA2B208027R45D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P500128

CATALOG NUMBER: LDA2B208027R45D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1836589
5°	1796110
10°	1666436
15°	1421155
20°	1069895
25°	645017
30°	310991
35°	140995
40°	64855
45°	33491
50°	17653
55°	6623
60°	1875
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500128

CATALOG NUMBER: LDA2B208027R45D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.2	18.2
10°-20°	759.8	41.0
20°-30°	542.8	29.3
30°-40°	162.7	8.8
40°-50°	40.4	2.2
50°-60°	8.4	0.5
60°-70°	1.3	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1639.8	88.5
0°-40°	1802.5	97.3
0°-60°	1851.3	99.9
0°-90°	1853.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1853.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3723	
5°	3627	337
15°	2782	760
25°	1185	543
35°	234	163
45°	48	40
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500128

CATALOG NUMBER: LDA2B208027R45D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3722.6
1°	3729.3
2°	3720.7
3°	3689.0
4°	3666.0
5°	3626.7
6°	3587.3
7°	3545.1
8°	3476.0
9°	3410.8
10°	3326.4
11°	3241.9
12°	3135.4
13°	3021.3
14°	2914.8
15°	2782.4
16°	2652.8
17°	2506.0
18°	2366.9
19°	2196.1
20°	2037.8
21°	1862.3
22.5°	1600.3
23°	1512.1
24°	1340.3
25°	1184.9
26°	1029.5
27°	887.5
28°	755.1
29°	646.7
30°	545.9
32.5°	358.8
35°	234.1
37.5°	153.5
40°	100.7
42.5°	68.1
45°	48.0
47.5°	34.5
50°	23.0
52.5°	14.4
55°	7.7
57.5°	3.8
60°	1.9
62.5°	1.9
65°	1.0



TEST NUMBER: P500128

CATALOG NUMBER: LDA2B208027R45D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)