

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280966

Luminaire Tested: **LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1590.8 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280966

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P280966

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1358570
5°	1330876
10°	1237603
15°	1080576
20°	894642
25°	684266
30°	374454
35°	138646
40°	47981
45°	21629
50°	10208
55°	5075
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280966

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	249.7	15.7
10°-20°	584.7	36.8
20°-30°	552.7	34.7
30°-40°	170.2	10.7
40°-50°	26.9	1.7
50°-60°	5.7	0.4
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.1	87.2
0°-40°	1557.3	97.9
0°-60°	1589.9	99.9
0°-90°	1590.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1590.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2754	
5°	2687	250
15°	2116	585
25°	1257	553
35°	230	170
45°	31	27
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280966

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2753.7
1°	2743.4
2°	2730.8
3°	2720.5
4°	2707.2
5°	2687.3
6°	2661.5
7°	2626.8
8°	2580.3
9°	2526.5
10°	2470.4
11°	2408.5
12°	2342.8
13°	2271.3
14°	2196.8
15°	2115.6
17.5°	1901.0
20°	1704.0
22.5°	1504.1
25°	1257.0
27.5°	959.0
30°	657.3
32.5°	403.5
35°	230.2
37.5°	128.4
40°	74.5
42.5°	46.5
45°	31.0
47.5°	20.7
50°	13.3
52.5°	8.9
55°	5.9
57.5°	3.7
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280966

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)