

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500175

Luminaire Tested: **LDA2B208027R65D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208027R65D010 2LBDLC1MB
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1942.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500175

CATALOG NUMBER: LDA2B208027R65D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P500175

CATALOG NUMBER: LDA2B208027R65D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1016424
5°	974051
10°	927551
15°	881582
20°	820089
25°	757048
30°	656904
35°	471287
40°	256005
45°	109333
50°	46973
55°	16945
60°	3059
65°	2452
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500175

CATALOG NUMBER: LDA2B208027R65D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	9.5
10°-20°	483.5	24.9
20°-30°	632.1	32.5
30°-40°	480.9	24.8
40°-50°	139.0	7.2
50°-60°	20.9	1.1
60°-70°	1.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1299.7	66.9
0°-40°	1780.6	91.7
0°-60°	1940.5	99.9
0°-90°	1942.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1942.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2060	
5°	1967	184
15°	1726	483
25°	1391	632
35°	782	481
45°	157	139
55°	20	21
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500175

CATALOG NUMBER: LDA2B208027R65D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2060.2
1°	2052.9
2°	2041.5
3°	2018.6
4°	1993.7
5°	1966.8
6°	1940.8
7°	1918.0
8°	1896.2
9°	1876.5
10°	1851.5
11°	1829.8
12°	1806.9
13°	1784.1
14°	1759.2
15°	1726.0
16°	1701.1
17°	1671.0
18°	1625.3
19°	1601.4
20°	1562.0
21°	1526.7
22.5°	1472.7
23°	1452.0
24°	1419.8
25°	1390.7
26°	1352.3
27°	1309.8
28°	1263.1
29°	1213.3
30°	1153.1
32.5°	988.0
35°	782.5
37.5°	577.1
40°	397.5
42.5°	252.2
45°	156.7
47.5°	97.6
50°	61.2
52.5°	36.3
55°	19.7
57.5°	7.3
60°	3.1
62.5°	2.1
65°	2.1



TEST NUMBER: P500175

CATALOG NUMBER: LDA2B208027R65D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)