

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315195

Luminaire Tested: **LDA2B20NFL9730D010 PIN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B20NFL9730D010 PIN1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1345.2 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315195

CATALOG NUMBER: LDA2B20NFL9730D010 PIN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P315195

CATALOG NUMBER: LDA2B20NFL9730D010 PIN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			97																
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			91																
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			89																
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			86																
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			84																
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			82																
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			80																
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			78																
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76			76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3443320
5°	3175569
10°	2139955
15°	1055089
20°	450681
25°	177191
30°	69729
35°	30596
40°	14684
45°	7117
50°	3914
55°	2150
60°	1283
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P315195

CATALOG NUMBER: LDA2B20NFL9730D010 PIN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	543.2	40.4
10°-20°	585.0	43.5
20°-30°	168.9	12.6
30°-40°	35.6	2.7
40°-50°	8.8	0.7
50°-60°	2.5	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.0	96.4
0°-40°	1332.7	99.1
0°-60°	1344.0	99.9
0°-90°	1345.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1345.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6979	
5°	6412	543
15°	2066	585
25°	326	169
35°	51	36
45°	10	9
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315195

CATALOG NUMBER: LDA2B20NFL9730D010 PIN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6979.3
1°	6935.5
2°	6861.3
3°	6761.0
4°	6618.9
5°	6412.1
6°	6133.0
7°	5768.8
8°	5320.9
9°	4798.8
10°	4271.6
11°	3738.7
12°	3235.6
13°	2788.9
14°	2396.2
15°	2065.7
17.5°	1365.3
20°	858.4
22.5°	527.8
25°	325.5
27.5°	198.6
30°	122.4
32.5°	77.4
35°	50.8
37.5°	33.6
40°	22.8
42.5°	15.9
45°	10.2
47.5°	6.3
50°	5.1
52.5°	3.8
55°	2.5
57.5°	1.9
60°	1.3
62.5°	1.3
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P315195
CATALOG NUMBER: LDA2B20NFL9730D010 PIN1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)