

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500187

Luminaire Tested: **LDA2B208027R70D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208027R70D010 2LBD1WMH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1881.4 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500187

CATALOG NUMBER: LDA2B208027R70D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P500187

CATALOG NUMBER: LDA2B208027R70D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	735109
5°	726972
10°	723354
15°	720844
20°	695133
25°	666411
30°	659695
35°	563376
40°	351580
45°	162638
50°	58947
55°	4129
60°	1875
65°	2218
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500187

CATALOG NUMBER: LDA2B208027R70D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	7.4
10°-20°	395.3	21.0
20°-30°	568.3	30.2
30°-40°	560.2	29.8
40°-50°	199.6	10.6
50°-60°	16.4	0.9
60°-70°	1.5	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.9	58.6
0°-40°	1663.1	88.4
0°-60°	1879.2	99.9
0°-90°	1881.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1881.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1490	
5°	1468	139
15°	1411	395
25°	1224	568
35°	935	560
45°	233	200
55°	5	16
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500187

CATALOG NUMBER: LDA2B208027R70D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1490.0
1°	1490.0
2°	1487.1
3°	1488.1
4°	1475.6
5°	1467.9
6°	1457.4
7°	1453.5
8°	1448.7
9°	1447.8
10°	1443.9
11°	1439.1
12°	1439.1
13°	1430.5
14°	1419.0
15°	1411.3
16°	1396.0
17°	1387.3
18°	1360.5
19°	1342.2
20°	1324.0
21°	1300.0
22.5°	1266.4
23°	1253.0
24°	1240.5
25°	1224.2
26°	1214.6
27°	1198.3
28°	1196.4
29°	1179.1
30°	1158.0
32.5°	1076.5
35°	935.4
37.5°	752.2
40°	545.9
42.5°	373.2
45°	233.1
47.5°	139.1
50°	76.8
52.5°	28.8
55°	4.8
57.5°	2.9
60°	1.9
62.5°	1.9
65°	1.9



TEST NUMBER: P500187

CATALOG NUMBER: LDA2B208027R70D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)