

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279203

Luminaire Tested: **LDA2B058027D010 EU2B05FL408027 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058027D010 EU2B05FL408027 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 847.2 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279203

CATALOG NUMBER: LDA2B058027D010 EU2B05FL408027 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279203

CATALOG NUMBER: LDA2B058027D010 EU2B05FL408027 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1164975
5°	1140354
10°	1039368
15°	811913
20°	480713
25°	178715
30°	55829
35°	24814
40°	11528
45°	5442
50°	2993
55°	1634
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279203

CATALOG NUMBER: LDA2B058027D010 EU2B05FL408027 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.8	25.1
10°-20°	423.3	50.0
20°-30°	173.3	20.5
30°-40°	28.7	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.5	95.5
0°-40°	838.1	98.9
0°-60°	846.7	99.9
0°-90°	847.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2361	
5°	2303	213
15°	1590	423
25°	328	173
35°	41	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279203

CATALOG NUMBER: LDA2B058027D010 EU2B05FL408027 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2361.3
1°	2353.2
2°	2342.3
3°	2332.5
4°	2319.7
5°	2302.6
6°	2277.3
7°	2244.2
8°	2197.2
9°	2140.0
10°	2074.7
11°	1998.8
12°	1913.3
13°	1815.6
14°	1707.1
15°	1589.6
17.5°	1260.6
20°	915.6
22.5°	586.1
25°	328.3
27.5°	173.1
30°	98.0
32.5°	62.2
35°	41.2
37.5°	27.2
40°	17.9
42.5°	11.7
45°	7.8
47.5°	5.4
50°	3.9
52.5°	2.7
55°	1.9
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279203

CATALOG NUMBER: LDA2B058027D010 EU2B05FL408027 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)