

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P277862

Luminaire Tested: **LDA2B058027D010 EU2B05SP158027 2LBAD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P277862  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 781.3 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P277862

CATALOG NUMBER: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P277862

CATALOG NUMBER: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93	93	93	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92	92	92	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90	90	90	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88	88	88	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86	86	86	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	85	85	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82	82	82	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3529609
5°	2814039
10°	1221722
15°	422097
20°	173048
25°	78171
30°	31447
35°	14635
40°	7986
45°	2930
50°	1765
55°	1290
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P277862

CATALOG NUMBER: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	429.4	55.0
10°-20°	257.9	33.0
20°-30°	71.0	9.1
30°-40°	16.9	2.2
40°-50°	4.1	0.5
50°-60°	1.4	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.3	97.1
0°-40°	775.2	99.2
0°-60°	780.7	99.9
0°-90°	781.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	781.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7154	
5°	5682	429
15°	826	258
25°	144	71
35°	24	17
45°	4	4
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P277862

CATALOG NUMBER: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7154.2
1°	7075.1
2°	6885.6
3°	6596.5
4°	6188.5
5°	5682.1
6°	5063.7
7°	4386.3
8°	3674.6
9°	3020.0
10°	2438.7
11°	1946.5
12°	1549.3
13°	1249.4
14°	1010.9
15°	826.4
17.5°	513.0
20°	329.6
22.5°	216.2
25°	143.6
27.5°	92.3
30°	55.2
32.5°	34.7
35°	24.3
37.5°	17.8
40°	12.4
42.5°	7.3
45°	4.2
47.5°	3.1
50°	2.3
52.5°	1.9
55°	1.5
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P277862

CATALOG NUMBER: LDA2B058027D010 EU2B05SP158027 2LBAD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)