

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279902

Luminaire Tested: **LDA2B208030D010 EU2B20FL408030 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279902  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2111.6 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279902

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279902

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96	96	96	96	96	96	96	96	96																
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92	92	92	92	92	92	92	92	92																
	3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85	85	85	85	85	85	85	85	85	85	85	85																
	5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82	82	82	82	82	82	82	82	82	82	82	82																
	6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79	79	79	79	79	79	79	79	79	79	79	79																
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77	77	77	77	77	77	77	77	77	77	77	77																
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74	74	74	74	74	74	74																
	9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72	72	72	72	72	72	72	72	72	72	72	72																
	10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69	69	69	69	69	69	69	69	69	69	69	69																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2903434
5°	2842070
10°	2590329
15°	2023552
20°	1198054
25°	445345
30°	139174
35°	61915
40°	28724
45°	13536
50°	7445
55°	4129
60°	1875
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279902

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	530.5	25.1
10°-20°	1054.9	50.0
20°-30°	432.0	20.5
30°-40°	71.5	3.4
40°-50°	16.9	0.8
50°-60°	4.5	0.2
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2017.4	95.5
0°-40°	2088.9	98.9
0°-60°	2110.3	99.9
0°-90°	2111.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2111.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5885	
5°	5739	530
15°	3962	1055
25°	818	432
35°	103	72
45°	19	17
55°	5	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279902

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5885.0
1°	5864.7
2°	5837.5
3°	5813.3
4°	5781.3
5°	5738.7
6°	5675.7
7°	5593.3
8°	5476.0
9°	5333.5
10°	5170.6
11°	4981.6
12°	4768.3
13°	4525.0
14°	4254.6
15°	3961.8
17.5°	3141.7
20°	2281.9
22.5°	1460.8
25°	818.1
27.5°	431.4
30°	244.3
32.5°	155.1
35°	102.8
37.5°	67.9
40°	44.6
42.5°	29.1
45°	19.4
47.5°	13.6
50°	9.7
52.5°	6.8
55°	4.8
57.5°	2.9
60°	1.9
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279902

CATALOG NUMBER: LDA2B208030D010 EU2B20FL408030 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)