

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279006

Luminaire Tested: **LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1956.6 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279006

CATALOG NUMBER: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279006

CATALOG NUMBER: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5008264
5°	4618816
10°	3112493
15°	1534596
20°	655493
25°	257702
30°	101461
35°	44449
40°	21382
45°	10326
50°	5680
55°	3183
60°	1776
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P279006

CATALOG NUMBER: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	790.0	40.4
10°-20°	850.8	43.5
20°-30°	245.7	12.6
30°-40°	51.9	2.7
40°-50°	12.8	0.7
50°-60°	3.7	0.2
60°-70°	1.2	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1886.5	96.4
0°-40°	1938.4	99.1
0°-60°	1954.8	99.9
0°-90°	1956.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1956.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10151	
5°	9326	790
15°	3004	851
25°	473	246
35°	74	52
45°	15	13
55°	4	4
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279006

CATALOG NUMBER: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10151.3
1°	10087.6
2°	9979.6
3°	9833.9
4°	9627.2
5°	9326.3
6°	8920.3
7°	8390.7
8°	7739.2
9°	6979.8
10°	6212.9
11°	5437.8
12°	4706.1
13°	4056.5
14°	3485.3
15°	3004.5
17.5°	1985.8
20°	1248.5
22.5°	767.7
25°	473.4
27.5°	288.8
30°	178.1
32.5°	112.6
35°	73.8
37.5°	48.9
40°	33.2
42.5°	23.1
45°	14.8
47.5°	9.2
50°	7.4
52.5°	5.5
55°	3.7
57.5°	2.8
60°	1.8
62.5°	1.8
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.9
80°	0.0
82.5°	0.0



TEST NUMBER: P279006

CATALOG NUMBER: LDA2B208030D010 EU2B20NFL258030 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)