

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491699

Luminaire Tested: **LDA2B058027R45D010 2LBDL1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P491699  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058027R45D010 2LBDL1MB  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 736.9 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P491699

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P491699

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	730274
5°	714195
10°	662637
15°	565111
20°	425427
25°	256505
30°	123679
35°	56073
40°	25826
45°	13326
50°	7061
55°	2666
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491699

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.1	18.2
10°-20°	302.1	41.0
20°-30°	215.8	29.3
30°-40°	64.7	8.8
40°-50°	16.1	2.2
50°-60°	3.4	0.5
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.0	88.5
0°-40°	716.8	97.3
0°-60°	736.2	99.9
0°-90°	736.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1480	
5°	1442	134
15°	1106	302
25°	471	216
35°	93	65
45°	19	16
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491699

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1480.2
1°	1482.9
2°	1479.5
3°	1466.9
4°	1457.7
5°	1442.1
6°	1426.4
7°	1409.6
8°	1382.2
9°	1356.2
10°	1322.7
11°	1289.1
12°	1246.7
13°	1201.3
14°	1159.0
15°	1106.4
16°	1054.9
17°	996.5
18°	941.2
19°	873.3
20°	810.3
21°	740.5
22.5°	636.3
23°	601.2
24°	533.0
25°	471.2
26°	409.4
27°	352.9
28°	300.2
29°	257.1
30°	217.1
32.5°	142.7
35°	93.1
37.5°	61.0
40°	40.1
42.5°	27.1
45°	19.1
47.5°	13.7
50°	9.2
52.5°	5.7
55°	3.1
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P491699

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)