

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491700

Luminaire Tested: **LDA2B058027R45D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058027R45D010 2LBDL1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 736.9 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491700

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P491700

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	730274
5°	714195
10°	662637
15°	565111
20°	425427
25°	256505
30°	123679
35°	56073
40°	25826
45°	13326
50°	7061
55°	2666
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491700

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	18.2
10°-20°	302.1	41.0
20°-30°	215.8	29.3
30°-40°	64.7	8.8
40°-50°	16.1	2.2
50°-60°	3.4	0.5
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.0	88.5
0°-40°	716.8	97.3
0°-60°	736.2	99.9
0°-90°	736.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1480	
5°	1442	134
15°	1106	302
25°	471	216
35°	93	65
45°	19	16
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491700

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1480.2
1°	1482.9
2°	1479.5
3°	1466.9
4°	1457.7
5°	1442.1
6°	1426.4
7°	1409.6
8°	1382.2
9°	1356.2
10°	1322.7
11°	1289.1
12°	1246.7
13°	1201.3
14°	1159.0
15°	1106.4
16°	1054.9
17°	996.5
18°	941.2
19°	873.3
20°	810.3
21°	740.5
22.5°	636.3
23°	601.2
24°	533.0
25°	471.2
26°	409.4
27°	352.9
28°	300.2
29°	257.1
30°	217.1
32.5°	142.7
35°	93.1
37.5°	61.0
40°	40.1
42.5°	27.1
45°	19.1
47.5°	13.7
50°	9.2
52.5°	5.7
55°	3.1
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P491700

CATALOG NUMBER: LDA2B058027R45D010 2LBDL1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)