

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280791

Luminaire Tested: **LDA2B208030D010 EU2B20WFL558030 2LBAD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280791  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2148.6 lumens  
Efficiency: N/A  
Efficacy: 104.3 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280791

CATALOG NUMBER: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P280791

CATALOG NUMBER: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1834960
5°	1797596
10°	1671596
15°	1459513
20°	1208344
25°	924222
30°	505709
35°	187250
40°	64790
45°	29165
50°	13739
55°	6881
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P280791

CATALOG NUMBER: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	337.3	15.7
10°-20°	789.8	36.8
20°-30°	746.5	34.7
30°-40°	229.8	10.7
40°-50°	36.3	1.7
50°-60°	7.7	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1873.5	87.2
0°-40°	2103.3	97.9
0°-60°	2147.4	99.9
0°-90°	2148.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2148.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3719	
5°	3630	337
15°	2858	790
25°	1698	746
35°	311	230
45°	42	36
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280791

CATALOG NUMBER: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3719.3
1°	3705.4
2°	3688.4
3°	3674.5
4°	3656.6
5°	3629.7
6°	3594.8
7°	3548.0
8°	3485.2
9°	3412.5
10°	3336.7
11°	3253.0
12°	3164.4
13°	3067.7
14°	2967.1
15°	2857.5
17.5°	2567.6
20°	2301.5
22.5°	2031.5
25°	1697.8
27.5°	1295.2
30°	887.7
32.5°	545.0
35°	310.9
37.5°	173.4
40°	100.6
42.5°	62.8
45°	41.8
47.5°	27.9
50°	17.9
52.5°	12.0
55°	8.0
57.5°	5.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280791

CATALOG NUMBER: LDA2B208030D010 EU2B20WFL558030 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)