

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491708

Luminaire Tested: **LDA2B058027R60D010 2LBD1B**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058027R60D010 2LBD1B
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 753.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491708
CATALOG NUMBER: LDA2B058027R60D010 2LBD1B

Luminous Intensity Polar Plot





TEST NUMBER: P491708

CATALOG NUMBER: LDA2B058027R60D010 2LBD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	450785
5°	427942
10°	418913
15°	405497
20°	370772
25°	329177
30°	246218
35°	139007
40°	52360
45°	23443
50°	11436
55°	2322
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491708

CATALOG NUMBER: LDA2B058027R60D010 2LBD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	10.9
10°-20°	220.5	29.3
20°-30°	269.4	35.8
30°-40°	146.9	19.5
40°-50°	29.4	3.9
50°-60°	4.2	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.7	75.9
0°-40°	718.6	95.4
0°-60°	752.3	99.9
0°-90°	753.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	914	
5°	864	82
15°	794	221
25°	605	269
35°	231	147
45°	34	29
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491708

CATALOG NUMBER: LDA2B058027R60D010 2LBD1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	913.7
1°	909.5
2°	901.5
3°	890.8
4°	875.5
5°	864.1
6°	858.0
7°	850.7
8°	845.0
9°	842.4
10°	836.2
11°	829.4
12°	823.3
13°	816.0
14°	805.3
15°	793.9
16°	779.4
17°	759.2
18°	746.2
19°	725.2
20°	706.2
21°	688.6
22.5°	659.2
23°	647.0
24°	628.3
25°	604.7
26°	574.5
27°	542.9
28°	506.6
29°	472.3
30°	432.2
32.5°	331.5
35°	230.8
37.5°	144.6
40°	81.3
42.5°	50.7
45°	33.6
47.5°	22.9
50°	14.9
52.5°	7.6
55°	2.7
57.5°	1.1
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P491708

CATALOG NUMBER: LDA2B058027R60D010 2LBD1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)