

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279229

Luminaire Tested: **LDA2B058030D010 EU2B05FL408030 2LBALD1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279229  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058030D010 EU2B05FL408030 2LBALD1B  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in ADJ spun Refl w/lens Self-Flanged, B  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 851.2 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279229

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P279229

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1170402
5°	1145653
10°	1044177
15°	815693
20°	482918
25°	179531
30°	56114
35°	24935
40°	11593
45°	5442
50°	2993
55°	1720
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279229

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.8	25.1
10°-20°	425.2	50.0
20°-30°	174.2	20.5
30°-40°	28.8	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	813.2	95.5
0°-40°	842.0	98.9
0°-60°	850.7	99.9
0°-90°	851.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	851.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2372	
5°	2313	214
15°	1597	425
25°	330	174
35°	41	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279229

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2372.3
1°	2364.1
2°	2353.1
3°	2343.3
4°	2330.5
5°	2313.3
6°	2287.9
7°	2254.6
8°	2207.4
9°	2149.9
10°	2084.3
11°	2008.1
12°	1922.1
13°	1824.0
14°	1715.0
15°	1597.0
17.5°	1266.4
20°	919.8
22.5°	588.9
25°	329.8
27.5°	173.9
30°	98.5
32.5°	62.5
35°	41.4
37.5°	27.4
40°	18.0
42.5°	11.7
45°	7.8
47.5°	5.5
50°	3.9
52.5°	2.7
55°	2.0
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279229

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1B

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)