

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279226

Luminaire Tested: **LDA2B058030D010 EU2B05FL408030 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058030D010 EU2B05FL408030 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279226

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279226

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1171537
5°	1146743
10°	1045179
15°	816510
20°	483390
25°	179695
30°	56171
35°	24995
40°	11593
45°	5442
50°	2993
55°	1720
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279226

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.0	25.1
10°-20°	425.6	50.0
20°-30°	174.3	20.5
30°-40°	28.9	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.0	95.5
0°-40°	842.9	98.9
0°-60°	851.5	99.9
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2375	
5°	2316	214
15°	1599	426
25°	330	174
35°	42	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279226

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2374.6
1°	2366.3
2°	2355.4
3°	2345.6
4°	2332.7
5°	2315.5
6°	2290.1
7°	2256.8
8°	2209.5
9°	2152.0
10°	2086.3
11°	2010.0
12°	1924.0
13°	1825.8
14°	1716.7
15°	1598.6
17.5°	1267.7
20°	920.7
22.5°	589.4
25°	330.1
27.5°	174.1
30°	98.6
32.5°	62.6
35°	41.5
37.5°	27.4
40°	18.0
42.5°	11.7
45°	7.8
47.5°	5.5
50°	3.9
52.5°	2.7
55°	2.0
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279226

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)