

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280128

Luminaire Tested: **LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 843.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280128

CATALOG NUMBER: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P280128

CATALOG NUMBER: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64		71	67	64		70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61		68	64	61		67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	719914
5°	705231
10°	655823
15°	572619
20°	474097
25°	362601
30°	198421
35°	73479
40°	25440
45°	11443
50°	5373
55°	2666
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280128

CATALOG NUMBER: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	15.7
10°-20°	309.9	36.8
20°-30°	292.9	34.7
30°-40°	90.2	10.7
40°-50°	14.2	1.7
50°-60°	3.0	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.1	87.2
0°-40°	825.2	97.9
0°-60°	842.5	99.9
0°-90°	843.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1459	
5°	1424	132
15°	1121	310
25°	666	293
35°	122	90
45°	16	14
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280128

CATALOG NUMBER: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1459.2
1°	1453.7
2°	1447.1
3°	1441.6
4°	1434.6
5°	1424.0
6°	1410.3
7°	1392.0
8°	1367.3
9°	1338.8
10°	1309.1
11°	1276.3
12°	1241.5
13°	1203.6
14°	1164.1
15°	1121.1
17.5°	1007.3
20°	903.0
22.5°	797.0
25°	666.1
27.5°	508.2
30°	348.3
32.5°	213.8
35°	122.0
37.5°	68.0
40°	39.5
42.5°	24.6
45°	16.4
47.5°	10.9
50°	7.0
52.5°	4.7
55°	3.1
57.5°	2.0
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280128

CATALOG NUMBER: LDA2B058030D010 EU2B05WFL558030 2LBALD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)