

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491791

Luminaire Tested: **LDA2B058030R20D010 2LBD1WH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P491791  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058030R20D010 2LBD1WH-30DEG TILT  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 507.3 lumens  
Efficiency: N/A  
Efficacy: 72.5 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P491791

CATALOG NUMBER: LDA2B058030R20D010 2LBD1WH-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P491791

CATALOG NUMBER: LDA2B058030R20D010 2LBD1WH-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	8042	8042	8042
5°	15402	7132	5200
10°	36821	6212	3507
15°	214522	4954	1379
20°	1070000	3045	420
25°	1951057	1034	0
30°	2288368	0	0
35°	2002894	0	0
40°	1479098	0	0
45°	533127	0	0
50°	111062	0	0
55°	25460	344	0
60°	8091	395	0
65°	1868	934	0
70°	0	1154	577
75°	0	1525	0
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P491791

CATALOG NUMBER: LDA2B058030R20D010 2LBD1WH-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.8	0.4
10°-20°	27.9	5.5
20°-30°	187.8	37.0
30°-40°	219.4	43.3
40°-50°	64.0	12.6
50°-60°	4.3	0.8
60°-70°	0.8	0.2
70°-80°	0.7	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.5	42.9
0°-40°	437.0	86.1
0°-60°	505.2	99.6
0°-90°	507.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	16	16	16	16	16	
5°	31	23	14	12	10	4
15°	420	47	10	5	3	219
25°	3584	74	2	0	0	1587
35°	3326	40	0	0	0	2043
45°	764	8	0	0	0	704
55°	30	2	0	0	0	38
65°	2	1	1	1	0	2
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P491791

CATALOG NUMBER: LDA2B058030R20D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3
2.5°	21.0	21.0	18.7	16.7	15.2	14.4	14.0	13.2	12.8
5°	31.1	27.2	22.6	17.5	14.4	13.2	12.1	10.9	10.5
7.5°	45.5	39.7	27.2	17.9	13.6	11.7	10.5	9.3	8.6
10°	73.5	57.2	33.4	17.9	12.4	10.1	8.6	7.4	7.0
12.5°	135.7	87.5	40.1	17.5	11.3	8.6	6.6	5.8	4.7
15°	420.0	181.2	47.4	16.7	9.7	6.6	5.1	3.1	2.7
17.5°	1086.1	423.1	52.9	14.8	7.8	4.7	2.3	1.9	1.9
20°	2038.0	767.2	60.7	12.8	5.8	3.1	1.6	1.2	0.8
21°	2325.0	938.7	64.6	12.1	5.1	1.9	1.2	0.4	0.4
22°	2771.0	1125.7	67.7	11.3	4.3	1.2	0.8	0.4	0.0
23°	3088.7	1245.1	70.8	10.1	3.1	1.2	0.4	0.0	0.0
24°	3406.4	1397.2	72.7	9.3	2.7	0.8	0.4	0.0	0.0
25°	3584.1	1523.9	73.5	8.6	1.9	0.4	0.0	0.0	0.0
26°	3730.3	1608.7	73.9	7.8	1.2	0.0	0.0	0.0	0.0
27°	3855.5	1707.1	73.1	7.0	1.2	0.0	0.0	0.0	0.0
28°	3926.7	1723.4	71.9	6.2	0.4	0.0	0.0	0.0	0.0
29°	3957.4	1703.6	68.4	5.4	0.4	0.0	0.0	0.0	0.0
30°	4016.9	1684.9	64.9	5.1	0.0	0.0	0.0	0.0	0.0
31°	3962.0	1623.1	60.7	4.3	0.0	0.0	0.0	0.0	0.0
32°	3747.4	1571.0	55.6	3.5	0.0	0.0	0.0	0.0	0.0
33°	3683.2	1464.0	50.2	3.1	0.0	0.0	0.0	0.0	0.0
34°	3562.3	1305.0	45.5	2.7	0.0	0.0	0.0	0.0	0.0
35°	3325.5	1173.6	39.7	2.3	0.0	0.0	0.0	0.0	0.0
36°	3160.2	1023.5	34.6	1.9	0.0	0.0	0.0	0.0	0.0
37°	2987.2	892.4	30.7	1.6	0.0	0.0	0.0	0.0	0.0
38°	2772.2	754.8	26.1	1.2	0.0	0.0	0.0	0.0	0.0
39°	2521.7	623.7	22.2	1.2	0.0	0.0	0.0	0.0	0.0
40°	2296.6	502.8	19.1	0.8	0.0	0.0	0.0	0.0	0.0
42.5°	1417.4	287.0	11.3	0.8	0.0	0.0	0.0	0.0	0.0
45°	764.1	174.2	8.2	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	351.9	81.3	5.8	0.4	0.0	0.0	0.0	0.0	0.0
50°	144.7	36.2	4.3	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	52.1	20.2	2.7	0.0	0.0	0.4	0.0	0.0	0.0
55°	29.6	11.7	1.6	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	14.0	6.6	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	8.2	3.5	0.4	0.4	0.4	0.8	0.4	0.0	0.0
62.5°	3.9	1.2	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.0
67.5°	0.4	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
70°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
72.5°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
77.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P491791

CATALOG NUMBER: LDA2B058030R20D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)