

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279907

Luminaire Tested: **LDA2B208035D010 EU2B20FL408035 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208035D010 EU2B20FL408035 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2195.9 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279907

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279907

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96	96	96	96	96	96	96	96	96																
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92	92	92	92	92	92	92	92	92																
	3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85	85	85	85	85	85	85	85	85	85	85	85																
	5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82	82	82	82	82	82	82	82	82	82	82	82																
	6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79	79	79	79	79	79	79	79	79	79	79	79																
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77	77	77	77	77	77	77	77	77	77	77	77																
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74	74	74	74	74	74	74																
	9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72	72	72	72	72	72	72	72	72	72	72	72																
	10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69	69	69	69	69	69	69	69	69	69	69	69																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3019423
5°	2955581
10°	2693830
15°	2104406
20°	1245883
25°	463145
30°	144700
35°	64384
40°	29883
45°	14094
50°	7752
55°	4301
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279907

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	551.7	25.1
10°-20°	1097.0	50.0
20°-30°	449.3	20.5
30°-40°	74.4	3.4
40°-50°	17.6	0.8
50°-60°	4.7	0.2
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2098.0	95.5
0°-40°	2172.4	98.9
0°-60°	2194.6	99.9
0°-90°	2195.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2195.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6120	
5°	5968	552
15°	4120	1097
25°	851	449
35°	107	74
45°	20	18
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279907

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6120.1
1°	6099.0
2°	6070.7
3°	6045.5
4°	6012.3
5°	5967.9
6°	5902.4
7°	5816.7
8°	5694.7
9°	5546.5
10°	5377.2
11°	5180.6
12°	4958.8
13°	4705.8
14°	4424.5
15°	4120.1
17.5°	3267.2
20°	2373.0
22.5°	1519.2
25°	850.8
27.5°	448.6
30°	254.0
32.5°	161.3
35°	106.9
37.5°	70.6
40°	46.4
42.5°	30.2
45°	20.2
47.5°	14.1
50°	10.1
52.5°	7.1
55°	5.0
57.5°	3.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279907

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)