

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279920

Luminaire Tested: **LDA2B208035D010 EU2B20FL408035 2LBALD1WHH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279920  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WHH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2164.4 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279920

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P279920

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2976057
5°	2913089
10°	2655105
15°	2074168
20°	1227980
25°	456504
30°	142649
35°	63420
40°	29433
45°	13885
50°	7599
55°	4301
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279920

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	543.7	25.1
10°-20°	1081.3	50.0
20°-30°	442.8	20.5
30°-40°	73.3	3.4
40°-50°	17.3	0.8
50°-60°	4.6	0.2
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2067.8	95.5
0°-40°	2141.2	98.9
0°-60°	2163.1	99.9
0°-90°	2164.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2164.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6032	
5°	5882	544
15°	4061	1081
25°	839	443
35°	105	73
45°	20	17
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279920

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6032.2
1°	6011.3
2°	5983.5
3°	5958.6
4°	5925.9
5°	5882.1
6°	5817.6
7°	5733.1
8°	5612.9
9°	5466.8
10°	5299.9
11°	5106.1
12°	4887.5
13°	4638.1
14°	4360.9
15°	4060.9
17.5°	3220.3
20°	2338.9
22.5°	1497.4
25°	838.6
27.5°	442.2
30°	250.4
32.5°	159.0
35°	105.3
37.5°	69.6
40°	45.7
42.5°	29.8
45°	19.9
47.5°	13.9
50°	9.9
52.5°	7.0
55°	5.0
57.5°	3.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279920

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WHH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)