

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491962

Luminaire Tested: **LDA2B058030R65D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058030R65D010 2LBDL1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 727.9 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491962

CATALOG NUMBER: LDA2B058030R65D010 2LBDL1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P491962

CATALOG NUMBER: LDA2B058030R65D010 2LBDL1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87					87			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80					80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74					74			
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69					69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64					64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60					60			
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56					56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52					52			
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49					49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	380826
5°	364947
10°	347525
15°	330312
20°	307244
25°	283668
30°	246104
35°	176590
40°	95897
45°	40956
50°	17577
55°	6365
60°	1184
65°	934
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491962

CATALOG NUMBER: LDA2B058030R65D010 2LBDL1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	9.5
10°-20°	181.1	24.9
20°-30°	236.8	32.5
30°-40°	180.2	24.8
40°-50°	52.1	7.2
50°-60°	7.8	1.1
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	487.0	66.9
0°-40°	667.1	91.7
0°-60°	727.0	99.9
0°-90°	727.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	772	
5°	737	69
15°	647	181
25°	521	237
35°	293	180
45°	59	52
55°	7	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491962

CATALOG NUMBER: LDA2B058030R65D010 2LBDL1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	771.9
1°	769.2
2°	764.9
3°	756.3
4°	747.0
5°	736.9
6°	727.2
7°	718.6
8°	710.4
9°	703.1
10°	693.7
11°	685.6
12°	677.0
13°	668.4
14°	659.1
15°	646.7
16°	637.3
17°	626.1
18°	608.9
19°	600.0
20°	585.2
21°	572.0
22.5°	551.8
23°	544.0
24°	532.0
25°	521.1
26°	506.7
27°	490.7
28°	473.2
29°	454.6
30°	432.0
32.5°	370.2
35°	293.2
37.5°	216.2
40°	148.9
42.5°	94.5
45°	58.7
47.5°	36.6
50°	22.9
52.5°	13.6
55°	7.4
57.5°	2.7
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P491962

CATALOG NUMBER: LDA2B058030R65D010 2LBDL1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)