

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279918

Luminaire Tested: **LDA2B208035D010 EU2B20FL408035 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2135.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279918

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279918

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2935651
5°	2873568
10°	2619085
15°	2046025
20°	1211337
25°	450298
30°	140712
35°	62577
40°	29046
45°	13675
50°	7522
55°	4215
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279918

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	536.4	25.1
10°-20°	1066.6	50.0
20°-30°	436.8	20.5
30°-40°	72.3	3.4
40°-50°	17.1	0.8
50°-60°	4.6	0.2
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2039.8	95.5
0°-40°	2112.1	98.9
0°-60°	2133.7	99.9
0°-90°	2135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5950	
5°	5802	536
15°	4006	1067
25°	827	437
35°	104	72
45°	20	17
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279918

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5950.3
1°	5929.8
2°	5902.3
3°	5877.8
4°	5845.5
5°	5802.3
6°	5738.6
7°	5655.3
8°	5536.7
9°	5392.7
10°	5228.0
11°	5036.9
12°	4821.2
13°	4575.2
14°	4301.8
15°	4005.8
17.5°	3176.6
20°	2307.2
22.5°	1477.0
25°	827.2
27.5°	436.2
30°	247.0
32.5°	156.8
35°	103.9
37.5°	68.6
40°	45.1
42.5°	29.4
45°	19.6
47.5°	13.7
50°	9.8
52.5°	6.9
55°	4.9
57.5°	2.9
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279918

CATALOG NUMBER: LDA2B208035D010 EU2B20FL408035 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)