

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491968

Luminaire Tested: **LDA2B058030R65D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058030R65D010 2LBDLC1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 787.3 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491968

CATALOG NUMBER: LDA2B058030R65D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P491968

CATALOG NUMBER: LDA2B058030R65D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56				56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52				52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	411957
5°	394761
10°	375930
15°	357281
20°	332393
25°	306858
30°	266214
35°	191044
40°	103755
45°	44305
50°	19035
55°	6881
60°	1283
65°	934
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491968

CATALOG NUMBER: LDA2B058030R65D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	9.5
10°-20°	195.9	24.9
20°-30°	256.2	32.5
30°-40°	194.9	24.8
40°-50°	56.3	7.2
50°-60°	8.5	1.1
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.8	66.9
0°-40°	721.7	91.7
0°-60°	786.5	99.9
0°-90°	787.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	835	
5°	797	75
15°	700	196
25°	564	256
35°	317	195
45°	64	56
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491968

CATALOG NUMBER: LDA2B058030R65D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	835.0
1°	832.0
2°	827.4
3°	818.2
4°	808.1
5°	797.1
6°	786.6
7°	777.4
8°	768.5
9°	760.5
10°	750.4
11°	741.6
12°	732.3
13°	723.1
14°	713.0
15°	699.5
16°	689.4
17°	677.2
18°	658.7
19°	649.1
20°	633.1
21°	618.8
22.5°	596.9
23°	588.5
24°	575.4
25°	563.7
26°	548.1
27°	530.9
28°	511.9
29°	491.7
30°	467.3
32.5°	400.5
35°	317.2
37.5°	233.9
40°	161.1
42.5°	102.2
45°	63.5
47.5°	39.5
50°	24.8
52.5°	14.7
55°	8.0
57.5°	2.9
60°	1.3
62.5°	0.8
65°	0.8



TEST NUMBER: P491968

CATALOG NUMBER: LDA2B058030R65D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)