

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491989

Luminaire Tested: **LDA2B058030R70D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P491989  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058030R70D010 2LBDL1WMH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 706.0 lumens  
Efficiency: N/A  
Efficacy: 100.9 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P491989

CATALOG NUMBER: LDA2B058030R70D010 2LBDL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P491989

CATALOG NUMBER: LDA2B058030R70D010 2LBDL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93					93			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85					85			
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72					72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66					66			
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61					61			
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56					56			
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52					52			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48					48			
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45					45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	279539
5°	277883
10°	276036
15°	270910
20°	261095
25°	249972
30°	238128
35°	196525
40°	127713
45°	66772
50°	31008
55°	11354
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P491989

CATALOG NUMBER: LDA2B058030R70D010 2LBDL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.1	7.5
10°-20°	149.1	21.1
20°-30°	211.5	30.0
30°-40°	197.8	28.0
40°-50°	79.6	11.3
50°-60°	13.9	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.7	58.6
0°-40°	611.5	86.6
0°-60°	705.0	99.8
0°-90°	706.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	567	
5°	561	53
15°	530	149
25°	459	212
35°	326	198
45°	96	80
55°	13	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491989

CATALOG NUMBER: LDA2B058030R70D010 2LBDL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	566.6
1°	567.3
2°	566.2
3°	563.8
4°	562.7
5°	561.1
6°	554.9
7°	556.8
8°	551.4
9°	550.2
10°	551.0
11°	546.0
12°	544.8
13°	538.6
14°	536.2
15°	530.4
16°	526.9
17°	519.9
18°	511.7
19°	507.1
20°	497.3
21°	490.0
22.5°	476.3
23°	472.8
24°	466.2
25°	459.2
26°	453.8
27°	446.0
28°	438.2
29°	428.9
30°	418.0
32.5°	379.9
35°	326.3
37.5°	262.9
40°	198.3
42.5°	141.5
45°	95.7
47.5°	63.0
50°	40.4
52.5°	25.3
55°	13.2
57.5°	4.3
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P491989

CATALOG NUMBER: LDA2B058030R70D010 2LBDL1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)