

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278353

Luminaire Tested: **LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278353  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, GPH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 786.7 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278353

CATALOG NUMBER: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P278353

CATALOG NUMBER: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			97																
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			91																
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			89																
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			86																
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			84																
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			82																
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			80																
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			78																
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76			76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2013557
5°	1856976
10°	1251380
15°	616954
20°	263510
25°	103593
30°	40789
35°	17888
40°	8630
45°	4117
50°	2303
55°	1290
60°	691
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278353

CATALOG NUMBER: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	317.6	40.4
10°-20°	342.1	43.5
20°-30°	98.8	12.6
30°-40°	20.9	2.7
40°-50°	5.1	0.7
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.4	96.4
0°-40°	779.3	99.1
0°-60°	785.9	99.9
0°-90°	786.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4081	
5°	3750	318
15°	1208	342
25°	190	99
35°	30	21
45°	6	5
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278353

CATALOG NUMBER: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4081.3
1°	4055.7
2°	4012.3
3°	3953.6
4°	3870.5
5°	3749.6
6°	3586.4
7°	3373.4
8°	3111.5
9°	2806.2
10°	2497.9
11°	2186.2
12°	1892.0
13°	1630.9
14°	1401.2
15°	1207.9
17.5°	798.4
20°	501.9
22.5°	308.7
25°	190.3
27.5°	116.1
30°	71.6
32.5°	45.3
35°	29.7
37.5°	19.7
40°	13.4
42.5°	9.3
45°	5.9
47.5°	3.7
50°	3.0
52.5°	2.2
55°	1.5
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278353

CATALOG NUMBER: LDA2B058035D010 EU2B05NFL258035 2LBALD1GPH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)