

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280132

Luminaire Tested: **LDA2B058035D010 EU2B05WFL558035 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280132  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 863.8 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280132

CATALOG NUMBER: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P280132

CATALOG NUMBER: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	737724
5°	722713
10°	672055
15°	586768
20°	485805
25°	371583
30°	203321
35°	75285
40°	26084
45°	11722
50°	5526
55°	2752
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280132

CATALOG NUMBER: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.6	15.7
10°-20°	317.5	36.8
20°-30°	300.1	34.7
30°-40°	92.4	10.7
40°-50°	14.6	1.7
50°-60°	3.1	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.2	87.2
0°-40°	845.6	97.9
0°-60°	863.3	99.9
0°-90°	863.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1495	
5°	1459	136
15°	1149	318
25°	683	300
35°	125	92
45°	17	15
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280132

CATALOG NUMBER: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1495.3
1°	1489.7
2°	1482.9
3°	1477.3
4°	1470.1
5°	1459.3
6°	1445.3
7°	1426.4
8°	1401.2
9°	1372.0
10°	1341.5
11°	1307.9
12°	1272.2
13°	1233.4
14°	1192.9
15°	1148.8
17.5°	1032.3
20°	925.3
22.5°	816.8
25°	682.6
27.5°	520.7
30°	356.9
32.5°	219.1
35°	125.0
37.5°	69.7
40°	40.5
42.5°	25.2
45°	16.8
47.5°	11.2
50°	7.2
52.5°	4.8
55°	3.2
57.5°	2.0
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280132

CATALOG NUMBER: LDA2B058035D010 EU2B05WFL558035 2LBAD1MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)