

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500457

Luminaire Tested: **LDA2B208035R20D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500457  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208035R20D010 2LBDLC1MMS  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2027.9 lumens  
Efficiency: N/A  
Efficacy: 98.4 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500457

CATALOG NUMBER: LDA2B208035R20D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P500457

CATALOG NUMBER: LDA2B208035R20D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82
9	94	88	85	82	93	88	84	82	87	84	82	86	84	82	86	83	81	81
10	92	86	83	80	91	86	83	80	85	82	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6703948
5°	5666411
10°	3452604
15°	1420439
20°	511427
25°	205117
30°	93200
35°	43846
40°	23121
45°	12489
50°	7292
55°	3613
60°	2072
65°	1284
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P500457

CATALOG NUMBER: LDA2B208035R20D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	943.8	46.5
10°-20°	816.3	40.3
20°-30°	196.8	9.7
30°-40°	50.5	2.5
40°-50°	15.1	0.7
50°-60°	4.3	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1956.9	96.5
0°-40°	2007.4	99.0
0°-60°	2026.8	99.9
0°-90°	2027.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2027.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13588	
5°	11442	944
15°	2781	816
25°	377	197
35°	73	50
45°	18	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500457

CATALOG NUMBER: LDA2B208035R20D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13588.3
1°	13470.1
2°	13188.3
3°	12759.8
4°	12207.8
5°	11441.6
6°	10650.0
7°	9776.2
8°	8868.5
9°	7850.1
10°	6891.8
11°	5890.2
12°	5012.1
13°	4181.5
14°	3419.5
15°	2781.0
16°	2253.3
17°	1819.5
18°	1468.1
19°	1207.4
20°	974.1
22.5°	600.5
25°	376.8
27.5°	244.9
30°	163.6
32.5°	107.7
35°	72.8
37.5°	50.7
40°	35.9
42.5°	25.3
45°	17.9
47.5°	13.7
50°	9.5
52.5°	6.3
55°	4.2
57.5°	3.2
60°	2.1
62.5°	1.1
65°	1.1
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P500457

CATALOG NUMBER: LDA2B208035R20D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)