

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492149

Luminaire Tested: **LDA2B058035R60D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492149  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058035R60D010 2LBD1WMH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 776.0 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492149

CATALOG NUMBER: LDA2B058035R60D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P492149

CATALOG NUMBER: LDA2B058035R60D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	464549
5°	441017
10°	431738
15°	417909
20°	382113
25°	339248
30°	253795
35°	143283
40°	53906
45°	24141
50°	11743
55°	2408
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P492149

CATALOG NUMBER: LDA2B058035R60D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	10.9
10°-20°	227.2	29.3
20°-30°	277.6	35.8
30°-40°	151.4	19.5
40°-50°	30.3	3.9
50°-60°	4.4	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.2	75.9
0°-40°	740.6	95.4
0°-60°	775.3	99.9
0°-90°	776.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	776.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	942	
5°	890	84
15°	818	227
25°	623	278
35°	238	151
45°	35	30
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492149

CATALOG NUMBER: LDA2B058035R60D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	941.6
1°	937.3
2°	929.1
3°	918.1
4°	902.3
5°	890.5
6°	884.2
7°	876.8
8°	870.9
9°	868.1
10°	861.8
11°	854.8
12°	848.5
13°	841.0
14°	830.0
15°	818.2
16°	803.2
17°	782.4
18°	769.0
19°	747.4
20°	727.8
21°	709.7
22.5°	679.4
23°	666.8
24°	647.6
25°	623.2
26°	592.1
27°	559.5
28°	522.1
29°	486.7
30°	445.5
32.5°	341.7
35°	237.9
37.5°	149.0
40°	83.7
42.5°	52.3
45°	34.6
47.5°	23.6
50°	15.3
52.5°	7.9
55°	2.8
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P492149

CATALOG NUMBER: LDA2B058035R60D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)