

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492151

Luminaire Tested: **LDA2B058035R60D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058035R60D010 2LBDL1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 715.8 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492151

CATALOG NUMBER: LDA2B058035R60D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P492151

CATALOG NUMBER: LDA2B058035R60D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	423650
5°	412590
10°	401229
15°	381338
20°	348459
25°	299237
30°	222633
35°	130696
40°	62278
45°	29095
50°	14506
55°	5075
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492151

CATALOG NUMBER: LDA2B058035R60D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	11.0
10°-20°	207.8	29.0
20°-30°	246.7	34.5
30°-40°	139.2	19.4
40°-50°	36.2	5.1
50°-60°	6.6	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.8	74.4
0°-40°	672.0	93.9
0°-60°	714.9	99.9
0°-90°	715.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	859	
5°	833	78
15°	747	208
25°	550	247
35°	217	139
45°	42	36
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492151

CATALOG NUMBER: LDA2B058035R60D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	858.7
1°	859.1
2°	853.2
3°	848.1
4°	838.2
5°	833.1
6°	824.1
7°	817.4
8°	811.1
9°	806.8
10°	800.9
11°	789.5
12°	778.9
13°	773.0
14°	759.2
15°	746.6
16°	732.1
17°	714.8
18°	698.3
19°	678.6
20°	663.7
21°	643.2
22.5°	609.4
23°	603.5
24°	574.8
25°	549.7
26°	521.7
27°	489.5
28°	457.7
29°	426.6
30°	390.8
32.5°	300.8
35°	217.0
37.5°	148.2
40°	96.7
42.5°	63.3
45°	41.7
47.5°	28.3
50°	18.9
52.5°	11.8
55°	5.9
57.5°	2.4
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P492151

CATALOG NUMBER: LDA2B058035R60D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)