

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492165

Luminaire Tested: **LDA2B058035R65D010 2LBD1H**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058035R65D010 2LBD1H
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.2 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492165
CATALOG NUMBER: LDA2B058035R65D010 2LBD1H

Luminous Intensity Polar Plot





TEST NUMBER: P492165

CATALOG NUMBER: LDA2B058035R65D010 2LBD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	432580
5°	397782
10°	380138
15°	365095
20°	336278
25°	311431
30°	285355
35°	209595
40°	99246
45°	32653
50°	10592
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P492165

CATALOG NUMBER: LDA2B058035R65D010 2LBD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	9.5
10°-20°	198.8	25.0
20°-30°	263.7	33.1
30°-40°	208.6	26.2
40°-50°	45.6	5.7
50°-60°	3.4	0.4
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.9	67.6
0°-40°	746.6	93.8
0°-60°	795.6	99.9
0°-90°	796.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	877	
5°	803	75
15°	715	199
25°	572	264
35°	348	209
45°	47	46
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492165

CATALOG NUMBER: LDA2B058035R65D010 2LBD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	876.8
1°	872.1
2°	855.9
3°	838.2
4°	819.8
5°	803.2
6°	792.6
7°	782.0
8°	774.9
9°	764.3
10°	758.8
11°	750.2
12°	740.3
13°	731.7
14°	721.9
15°	714.8
16°	696.7
17°	687.7
18°	672.7
19°	659.0
20°	640.5
21°	625.5
22.5°	605.9
23°	600.4
24°	585.4
25°	572.1
26°	563.8
27°	550.0
28°	536.7
29°	520.6
30°	500.9
32.5°	432.5
35°	348.0
37.5°	248.1
40°	154.1
42.5°	86.9
45°	46.8
47.5°	25.2
50°	13.8
52.5°	5.9
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4



TEST NUMBER: P492165

CATALOG NUMBER: LDA2B058035R65D010 2LBD1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)