

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492207

Luminaire Tested: **LDA2B058035R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058035R70D010 2LBDLC1MMS  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 771.0 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492207

CATALOG NUMBER: LDA2B058035R70D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P492207

CATALOG NUMBER: LDA2B058035R70D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	305243
5°	303487
10°	301435
15°	295835
20°	285141
25°	272999
30°	260061
35°	214594
40°	139499
45°	72912
50°	33925
55°	12386
60°	1283
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492207

CATALOG NUMBER: LDA2B058035R70D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.0	7.5
10°-20°	162.8	21.1
20°-30°	231.0	30.0
30°-40°	216.1	28.0
40°-50°	86.9	11.3
50°-60°	15.2	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.7	58.6
0°-40°	667.8	86.6
0°-60°	769.9	99.9
0°-90°	771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	619	
5°	613	58
15°	579	163
25°	502	231
35°	356	216
45°	104	87
55°	14	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492207

CATALOG NUMBER: LDA2B058035R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	618.7
1°	619.5
2°	618.3
3°	615.7
4°	614.5
5°	612.8
6°	606.0
7°	608.1
8°	602.1
9°	600.9
10°	601.7
11°	596.2
12°	594.9
13°	588.1
14°	585.6
15°	579.2
16°	575.4
17°	567.7
18°	558.8
19°	553.7
20°	543.1
21°	535.0
22.5°	520.2
23°	516.4
24°	509.1
25°	501.5
26°	495.6
27°	487.1
28°	478.6
29°	468.4
30°	456.5
32.5°	414.9
35°	356.3
37.5°	287.1
40°	216.6
42.5°	154.6
45°	104.5
47.5°	68.8
50°	44.2
52.5°	27.6
55°	14.4
57.5°	4.7
60°	1.3
62.5°	0.8
65°	0.8



TEST NUMBER: P492207

CATALOG NUMBER: LDA2B058035R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)