

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500608

Luminaire Tested: **LDA2B208035R65D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208035R65D010 2LBDLC1MMS
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2002.1 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500608

CATALOG NUMBER: LDA2B208035R65D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P500608

CATALOG NUMBER: LDA2B208035R65D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1047506
5°	1003815
10°	955956
15°	908550
20°	845185
25°	780238
30°	676957
35°	485742
40°	263862
45°	112682
50°	48431
55°	17461
60°	3158
65°	2452
70°	1587
75°	0
80°	0
85°	0



TEST NUMBER: P500608

CATALOG NUMBER: LDA2B208035R65D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.8	9.5
10°-20°	498.3	24.9
20°-30°	651.5	32.5
30°-40°	495.6	24.8
40°-50°	143.3	7.2
50°-60°	21.5	1.1
60°-70°	1.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1339.5	66.9
0°-40°	1835.1	91.7
0°-60°	1999.9	99.9
0°-90°	2002.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2002.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2123	
5°	2027	190
15°	1779	498
25°	1433	651
35°	806	496
45°	162	143
55°	20	22
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500608

CATALOG NUMBER: LDA2B208035R65D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2123.2
1°	2115.7
2°	2103.9
3°	2080.4
4°	2054.7
5°	2026.9
6°	2000.2
7°	1976.6
8°	1954.2
9°	1933.9
10°	1908.2
11°	1885.7
12°	1862.2
13°	1838.7
14°	1813.0
15°	1778.8
16°	1753.1
17°	1722.1
18°	1675.0
19°	1650.4
20°	1609.8
21°	1573.4
22.5°	1517.8
23°	1496.4
24°	1463.2
25°	1433.3
26°	1393.7
27°	1349.9
28°	1301.7
29°	1250.4
30°	1188.3
32.5°	1018.3
35°	806.5
37.5°	594.7
40°	409.7
42.5°	259.9
45°	161.5
47.5°	100.5
50°	63.1
52.5°	37.4
55°	20.3
57.5°	7.5
60°	3.2
62.5°	2.1
65°	2.1



TEST NUMBER: P500608

CATALOG NUMBER: LDA2B208035R65D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)