

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500620

Luminaire Tested: **LDA2B208035R70D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500620
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208035R70D010 2LBDL1B
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1795.3 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500620
CATALOG NUMBER: LDA2B208035R70D010 2LBDL1B

Luminous Intensity Polar Plot





TEST NUMBER: P500620

CATALOG NUMBER: LDA2B208035R70D010 2LBDL1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	710786
5°	706617
10°	701913
15°	688870
20°	663999
25°	635709
30°	605518
35°	499654
40°	324788
45°	169685
50°	78903
55°	28901
60°	2960
65°	2335
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500620

CATALOG NUMBER: LDA2B208035R70D010 2LBDL1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	7.5
10°-20°	379.0	21.1
20°-30°	537.9	30.0
30°-40°	503.0	28.0
40°-50°	202.3	11.3
50°-60°	35.4	2.0
60°-70°	1.7	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1051.9	58.6
0°-40°	1554.9	86.6
0°-60°	1792.6	99.9
0°-90°	1795.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1795.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1441	
5°	1427	135
15°	1349	379
25°	1168	538
35°	830	503
45°	243	202
55°	34	35
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500620

CATALOG NUMBER: LDA2B208035R70D010 2LBDL1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1440.7
1°	1442.6
2°	1439.7
3°	1433.7
4°	1430.8
5°	1426.8
6°	1411.0
7°	1415.9
8°	1402.1
9°	1399.1
10°	1401.1
11°	1388.2
12°	1385.3
13°	1369.5
14°	1363.5
15°	1348.7
16°	1339.8
17°	1322.0
18°	1301.2
19°	1289.4
20°	1264.7
21°	1245.9
22.5°	1211.3
23°	1202.4
24°	1185.5
25°	1167.8
26°	1153.9
27°	1134.1
28°	1114.4
29°	1090.6
30°	1062.9
32.5°	966.0
35°	829.6
37.5°	668.4
40°	504.3
42.5°	359.9
45°	243.2
47.5°	160.2
50°	102.8
52.5°	64.3
55°	33.6
57.5°	10.9
60°	3.0
62.5°	2.0
65°	2.0



TEST NUMBER: P500620

CATALOG NUMBER: LDA2B208035R70D010 2LBDL1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)