

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279250

Luminaire Tested: **LDA2B058040D010 EU2B05FL408040 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058040D010 EU2B05FL408040 2LBAD1H
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 901.8 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279250

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P279250

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1240114
5°	1213898
10°	1106398
15°	864318
20°	511689
25°	190201
30°	59418
35°	26440
40°	12237
45°	5791
50°	3147
55°	1806
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279250

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.6	25.1
10°-20°	450.6	50.0
20°-30°	184.5	20.5
30°-40°	30.5	3.4
40°-50°	7.2	0.8
50°-60°	1.9	0.2
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.7	95.5
0°-40°	892.2	98.9
0°-60°	901.3	99.9
0°-90°	901.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2514	
5°	2451	227
15°	1692	451
25°	349	185
35°	44	31
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279250

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2513.6
1°	2504.9
2°	2493.3
3°	2483.0
4°	2469.3
5°	2451.1
6°	2424.2
7°	2389.0
8°	2338.9
9°	2278.0
10°	2208.5
11°	2127.7
12°	2036.7
13°	1932.7
14°	1817.2
15°	1692.2
17.5°	1341.9
20°	974.6
22.5°	624.0
25°	349.4
27.5°	184.2
30°	104.3
32.5°	66.2
35°	43.9
37.5°	29.0
40°	19.0
42.5°	12.4
45°	8.3
47.5°	5.8
50°	4.1
52.5°	2.9
55°	2.1
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279250

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)