

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279261

Luminaire Tested: **LDA2B058040D010 EU2B05FL408040 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058040D010 EU2B05FL408040 2LBALD1B
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 895.8 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279261

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P279261

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|--|--|--|--|--|--|----|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | | | | | |
| | 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | | | | | |
| | 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | 89 | | | | | | | |
| | 4 | 103 | 98 | 93 | 90 | 102 | 97 | 93 | 90 | 95 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | 4 | 103 | 98 | 93 | 90 | 102 | 97 | 93 | 90 | 95 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | 85 | | | | | | | |
| | 5 | 100 | 94 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 88 | 85 | 90 | 87 | 84 | 88 | 86 | 83 | 82 | 5 | 100 | 94 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 88 | 85 | 90 | 87 | 84 | 88 | 86 | 83 | 82 | 82 | | | | | | | |
| | 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 82 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 82 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | 79 | | | | | | | |
| | 7 | 94 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 81 | 78 | 83 | 80 | 78 | 77 | 7 | 94 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 81 | 78 | 83 | 80 | 78 | 77 | 77 | | | | | | | |
| | 8 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | 8 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | 74 | | | | | | | |
| | 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | 72 | 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | 72 | 72 | | | | | | | |
| | 10 | 85 | 78 | 74 | 71 | 84 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | 10 | 85 | 78 | 74 | 71 | 84 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | 69 | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1231776 |
| 5° | 1205727 |
| 10° | 1098934 |
| 15° | 858495 |
| 20° | 508276 |
| 25° | 188949 |
| 30° | 59019 |
| 35° | 26260 |
| 40° | 12172 |
| 45° | 5721 |
| 50° | 3147 |
| 55° | 1806 |
| 60° | 789 |
| 65° | 467 |
| 70° | 577 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P279261

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBALD1B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 225.0 | 25.1 |
| 10°-20° | 447.5 | 50.0 |
| 20°-30° | 183.3 | 20.5 |
| 30°-40° | 30.3 | 3.4 |
| 40°-50° | 7.2 | 0.8 |
| 50°-60° | 1.9 | 0.2 |
| 60°-70° | 0.4 | 0.0 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 855.9 | 95.5 |
| 0°-40° | 886.2 | 98.9 |
| 0°-60° | 895.3 | 99.9 |
| 0°-90° | 895.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 895.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2497 | |
| 5° | 2435 | 225 |
| 15° | 1681 | 448 |
| 25° | 347 | 183 |
| 35° | 44 | 30 |
| 45° | 8 | 7 |
| 55° | 2 | 2 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P279261

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBALD1B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2496.7 |
| 1° | 2488.1 |
| 2° | 2476.5 |
| 3° | 2466.3 |
| 4° | 2452.7 |
| 5° | 2434.6 |
| 6° | 2407.9 |
| 7° | 2372.9 |
| 8° | 2323.1 |
| 9° | 2262.7 |
| 10° | 2193.6 |
| 11° | 2113.4 |
| 12° | 2022.9 |
| 13° | 1919.7 |
| 14° | 1805.0 |
| 15° | 1680.8 |
| 17.5° | 1332.9 |
| 20° | 968.1 |
| 22.5° | 619.8 |
| 25° | 347.1 |
| 27.5° | 183.0 |
| 30° | 103.6 |
| 32.5° | 65.8 |
| 35° | 43.6 |
| 37.5° | 28.8 |
| 40° | 18.9 |
| 42.5° | 12.3 |
| 45° | 8.2 |
| 47.5° | 5.8 |
| 50° | 4.1 |
| 52.5° | 2.9 |
| 55° | 2.1 |
| 57.5° | 1.2 |
| 60° | 0.8 |
| 62.5° | 0.4 |
| 65° | 0.4 |
| 67.5° | 0.4 |
| 70° | 0.4 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P279261

CATALOG NUMBER: LDA2B058040D010 EU2B05FL408040 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)